

0 601 6A1 001 – GKS 12V-26

Material number	0 601 6A1 001	0 601 6A1 070
EAN	3165140755849	3165140755832
1 x circular saw blade, Standard for Wood, 85 x 15 x 1.1 mm, 20 2 608 643 071	✓	✓
1/2 L-BOXX inlay for charger 1 600 A00 2WY		✓
1/2 L-BOXX inlay for tool 1 600 A00 2WU	✓	✓
2 x battery GBA 12V 2.0Ah 1 600 Z00 02X		✓
Allen key	✓	✓
Cardboard box	✓	
Dust extraction adapter	✓	✓
L-BOXX 136 1 600 A00 1RR		✓
Parallel guide/guide rail adapter 1 619 P10 829	✓	✓
Quick charger GAL 1230 CV 1 600 A01 16B		✓
Packaging dimensions (width x length x height)	207 x 335 x 130 mm	360 x 440 x 155 mm
Battery voltage	12.0 V	12.0 V
Weight incl. battery	1,4 kg	1,4 kg
Battery capacity		2,0 Ah

Technical data

Technical data

No-load speed	1.400 rpm
Saw blade diameter	85 mm
Saw blade bore diameter	15 mm
Battery voltage	12 V

Cutting depth

Cutting depth (90°)	26.5 mm
Cutting depth (45°)	17 mm

Noise/vibration information

Sound pressure level	90 dB(A)
Sound power level	101 dB(A)
Uncertainty K	3 dB



Sales information

Positioning

- The smallest professional universal saw

User benefit incl. Reason to believe

- The most compact design in its class for perfect handling and versatile applications in wood
- Excellent ergonomics: small grip circumference and light weight (only 1.4 kg) for maximum comfort
- Practical battery charge level indicator can be used at any time to find out how much energy is left in the battery