

ROS300 | 300W Corded Random Orbit Sander

Article: 5133001145



- Random orbital sander delivers the perfect combination of quick stock removal and fine surface finish.
- Ideal for light to medium weight applications such as fine finishing and paint removal.
- Powerful 300W motor for maximum performance.
- Variable speed (7,000-12,000 rpm) to optimise surface finish.
- Quick fit hook and loop sanding sheet attachment.
- Cyclonic action dust box for efficient dust collection.
- Livetool Indicator™ glows blue when plugged into the power supply.

	ROS300
Diameter of orbit (mm)	2.4
Sanding pad size (mm)	125
Sound pressure level (dB(A))	88.6
Sound pressure level uncertainty [dB(A)]	3
Sound power level [dB(A)]	99.6
Sound power level uncertainty [dB(A)]	3
Vibration level [m/s ²]	14.68
Vibration uncertainty [m/s ²]	1.5
No load speed (rpm)	7,000-12,000
Supplied in	Recyclable Carton
Weight [without battery] [Kg]	1.7
Power	300W
Article Number	5133001145
Weight (kg)	1.7
Power input (W)	300