

## P620 | 18V Cordless Speed Sprayer

Article: 5133000155



- Ideal for painting fences, exterior walls, garage doors and outbuildings.
- Choose between three spray patterns, horizontal, vertical or round, to provide you with the best coverage whilst minimising overspray.
- Suitable for use with any brand paint.
- Highly versatile spray system that can be used with varnishes, wood preservatives, enamels, as well as oil-based and water-based paints.
- Innovative and patented delivery system also minimizes the need for dilution.
- Cordless convenience means paint projects have no limits. Spray up to 4m<sup>2</sup> per minute.
- GripZone™ overmould technology for improved comfort with a positive grip.

|  | P620              |
|--|-------------------|
| Sound pressure level (dB(A))                 | 83.0              |
| Sound pressure level uncertainty [dB(A)]     | 3.0               |
| Sound power level [dB(A)]                    | 94.0              |
| Sound power level uncertainty [dB(A)]        | 3.0               |
| Vibration level [m/s <sup>2</sup> ]          | 7.4               |
| Vibration uncertainty [m/s <sup>2</sup> ]    | 1.5               |
| Voltage (V)                                  | 18                |
| Container capacity (ml)                      | 1000              |
| Area flow rate sprayer (m <sup>2</sup> /min) | 4                 |
| Paint coverage sprayer (m <sup>2</sup> /min) | 10                |
| Flow rate (l/h)                              | 20                |
| Supplied in                                  | Recyclable Carton |
| Charger supplied                             | -                 |
| No. of batteries supplied                    | 0                 |
| Weight [without battery] [Kg]                | 2                 |
| Charger included?                            | No                |
| Power  | 18V               |
| Article Number                               | 5133000155        |
| Weight with battery pack (kg)                | 2.4               |
| Weight (kg)                                  | 2.4               |