






### EXTERNAL PIR DETECTORS

- ABS construction
- Time on adjustable: 5 sec - 5 min
- Vertically & horizontally adjustable detector
- 1000W incandescent / 300W fluorescent maximum load capacity
- Maximum 200W LED load capacity (no more than eight lights)
- 110° / 180° detection zone
- Adjustable lux level
- 12 metre range
- M.O.M: 1 / O.P.Q: 30



Code	Version	Colour	IP Rating
PIR110BK	110° PIR	Black	IP44
PIR110WH		White	
PIR180BK	180° PIR	Black	
PIR180WH		White	