

## GALEO

**Galeo is a stylish and innovative keypad, combining good looks with a high level of ruggedness and vandal resistance.**

Galeo is ideally suited for use internally or externally. Clever innovation has resulted in a keypad which can easily cope in the harshest of environments - and with the benefit of soft blue backlighting and a modern but uncompromising design, it truly is a keypad for all your coded entry solutions.

Galeo is supplied with a remote electronic controller - this means the electronics are housed in the secure area and therefore does not allow the possibility of gaining entry by "tampering" with the electronics within the keypad body.

To enhance the Galeo's flexibility, the unit can include "free voltage" technology. This means that any voltage between 12 and 48Vdc or 12 and 24Vac can be used. Additionally, there is the option of models with 2 or 3 relays to allow for additional switching or door/gate operation.



### Overview

- Backlit for convenience
- Heavy duty Zamak
- IP64, IK10
- 3 timed/latching relays
- Secure surface mount
- Free voltage
- Torx® mounting screws
- 100 user codes

## GALEO - Technical Specifications

### Product Specifications

Material: heavy duty Zamak

IP Rating: IP64

IK Rating: IK10

### Output Specifications

2 or 3 relays (pulse, timed or latched)

### Electrical Specifications

Operating voltage: 12V to 24Vac / 12V to 48Vdc

Current: 30 to 100mA

### Dimensions

Dimensions: 110 x 75 x 15mm

Environment: -25°C to 70°C