

For slotted and Phillips screws.



260P PicoFinish slotted screwdriver.
Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for sensitive and fast screw fixing.

Application: Ideal for fine and delicate fastening tasks for electronics, precision mechanics, model-making and hobby activities.

Order-No.	⊖	↔	⊕	●	↔	↔	↔
00475	0.8	40	0.16	2.0	134	9	10
00476	1.0	40	0.18	2.0	134	9	10
00477	1.2	40	0.2	2.0	134	9	10
00478	1.5	40	0.25	2.0	134	9	10
00479	1.5	60	0.25	2.0	154	9	10
00480	1.8	40	0.3	2.0	134	9	10
00481	1.8	60	0.3	2.0	154	9	10
00482	2.0	40	0.4	2.0	140	18	10
00484	2.0	60	0.4	2.0	160	18	10
00485	2.0	100	0.4	2.0	200	18	10
00486	2.5	50	0.4	2.5	150	18	10
00487	2.5	75	0.4	2.5	175	18	10
00488	2.5	100	0.4	2.5	200	18	10
00490	3.0	50	0.5	3.0	150	18	10
00492	3.0	100	0.5	3.0	200	18	10
00493	3.0	150	0.5	3.0	250	18	10
00495	3.5	60	0.6	3.5	160	18	10
00497	4.0	60	0.8	4.0	160	18	10
00498	4.0	100	0.8	4.0	200	18	10
00499	4.0	150	0.8	4.0	250	18	10



261P PicoFinish Phillips screwdriver.
Handle with rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for sensitive and fast screw fixing.

Application: Ideal for fine and delicate fastening tasks for electronics, precision mechanics, model-making and hobby activities.

Order-No.	⊕	↔	●	↔	↔	↔
00513	PH000	40	2.0	134	9	10
00512	PH00	40	2.0	134	9	10
00514	PH00	60	2.0	154	9	10
00511	PH0	50	3.0	150	18	10
00515	PH0	75	3.0	175	18	10
00516	PH1	60	4.0	160	18	10
00517	PH1	80	4.0	180	18	10
00518	PH1	150	4.0	250	18	10

For Pozidriv and TORX® screws.



262P PicoFinish Pozidriv screwdriver.
Handle with rotating cap and rapid-turning zone.

Order-No.	⊕	↔	●	↔	↔	↔
04461	PZ0	50	3.0	150	18	10
04462	PZ1	60	4.0	160	18	10



267P PicoFinish TORX® screwdriver.
Handle with rotating cap and rapid-turning zone.

Order-No.	⊕	↔	●	↔	↔	↔
25673	T1	40	2.5	134	9	10
25674	T2	40	2.5	134	9	10
20122	T3	40	2.5	134	9	10
20123	T4	40	2.5	134	9	10
00566	T5	40	2.5	134	9	10
00567	T6	40	2.5	140	18	10
00568	T7	40	2.5	140	18	10
00569	T8	40	2.5	140	18	10
00570	T9	50	3.0	150	18	10
00571	T10	50	3.0	150	18	10
00572	T15	60	3.5	160	18	10
00573	T20	60	4.0	160	18	10



267PR PicoFinish TORX® MagicSpring® screwdriver.
Handle with rotating cap and rapid-turning zone.
Retaining spring holds TORX® screws in place.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for sensitive and fast screw fixing.

Application: Ideal for fine and delicate fastening tasks for electronics, precision mechanics, model-making and hobby activities.

Order-No.	⊕	↔	●	↔	↔	↔
27729	T6	40	2.5	140	18	10
27730	T7	40	2.5	140	18	10
27731	T8	40	2.5	140	18	10
27732	T9	50	3.0	150	18	10
27733	T10	50	3.0	150	18	10
27734	T15	60	3.5	160	18	10