

Joker Ratcheting Combination / Double Open-Ended Wrench Set



Ratcheting Combination/Double Open-Ended Wrench Set
6-piece set




Practical configuration in a robust pouch

Application:

Hexagonal bolts and nuts

Design:

Ratcheting combination and double open-ended wrench; holding function with the metal plate in the jaw reduces the danger of losing bolts and nuts; exchangeable metal plate in the jaw with extra hard teeth secures bolts and nuts and reduces the risk of slipping; the integrated limit stop can prevent any slipping downwards from the screw head and allows a higher torque to be applied; the double-hex geometry creates a form-fitting connection with the nut or bolt and thereby lowers the risk of any slipping; a return angle of only 30° to avoid the need for any time-consuming turning of the wrench in screwdriving applications; special forged geometry for high torque transfer and great rigidity against bending; high performance chrome-molybdenum steel; nickel-chrome coating for enhanced corrosion resistance Ratcheting combination wrench: Ratcheting mechanism on the ring side with an exceptional 80 fine-tooth system for flexibility even in confined spaces

 	
Code	

05020022001	Joker	1 x 10x159; 1 x 13x177; 1 x 17x224; 1 x 19x246	RS-Nr. 8126217
	Joker	1 x 10x13x167; 1 x 17x19x235	
	Double		