



TC-LD 50

Laser Measuring Tool

Item No.: 2270080

Ident No.: 11016

Bar Code: 4006825616194

The Einhell TC-LD 50 laser distance meter offers easy and precise measurement of distances up to 50 meters, so it can be used to measure distances and also calculate areas and volumes. The interface for measuring can be set for measuring from either the front edge, rear edge or stop plate. Results can be added and subtracted, and there is an integrated Pythagoras function and min/max function for continuous measurements. The pitch function allows measurements of predefined distances, for example for staking out fence posts. The last 20 measurement results are saved automatically. A safety function ensures that the laser is only activated after the switching on operation is repeated. It switches off automatically after 3 minutes without bei

Features

- Easy and precise measurement of distances up to 50 m
- Measurements from the front edge, back edge or stop plate
- Easy measurement of lengths, areas and volumes
- Addition and subtraction of lengths, areas and volumes
- Min/max function for continuous measurements
- Safety function: laser radiation only with repeated power-up
- Pythagoras function: indirect measurement of lengths and heights
- Pitch function: precise investigation of defined distances
- Last 20 measurements saved automatically
- Comfortable handling thanks to the soft grip
- Automatic switch-off after 3 minutes of inactivity
- Incl. practical bag for storage
- 2x 1.5V AAA batteries needed (not included in delivery)



Technical Data

- | | |
|--------------------------|---------------|
| - Working range | 0.05 m - 50 m |
| - Measurement accuracy | +/- 2 mm/m |
| - Laser type class | II |
| - Laser diode | 635 nm |
| - Automatic deactivation | 3 min |

Logistic Data

- | | |
|--------------------------------------|-----------------------|
| - Product weight (kg) | 0.12 |
| - Gross weight (kg) | 0.31 |
| - Dimensions single packaging | 120 x 540 x 270 mm |
| - Pieces per export carton | 10 Pieces |
| - Gross weight of export carton | 3.3 kg |
| - Dimensions export carton | 365 x 245 x 220 mm |
| - Container quantity (20"/40"/40"HC) | 13800 28200 33840 |

