

Product information

10MM ANGLE DRILL



Satisfying the professional's needs

DA3010F

Input wattage	450 w
No Load Speed	0 - 2400 rpm
Vibration: Drilling	2.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Noise sound pressure	81 dB(A)
Noise sound power	92 dB(A)
Noise K factor	3 dB(A)
Net weight	1.6 kg



STANDARD EQUIPMENT: Chuck key, Side handle

- Forward/reverse rotation
- Variable speed
- Double Insulation
- LED job light for improved work visibility.

Details correct as of: 12-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com