

GP Batteries

PRODUCT SPECIFICATION

**GP Portable PowerBank
Model : RP10AB**

Revision History


Revision	Date	Initiator	Reason for Change
0.0	20 Mar 2017	CC Li	Preliminary release

Prepared By CC Li	Approved By Wilfred Kong
Date: 20 Mar 2017	Date: 20 Mar 2017

GP Batteries

Product Specification

Model no.: RP10AB



Product Name	:	GP Portable PowerBank RP10AB
Description	:	Back up power for USB powered electronic devices (e.g. smartphones, tablet PCs)
Battery Rating	:	Lithium Polymer 3.7V 10000mAh 37Wh
Input	:	2A / 5V DC
Output 1 & 2	:	Total 2.4A / 5V DC
Application	:	Charge USB powered electronic devices
Recharging Time	:	8 hours (approx.) by 5V/2A adaptor;
Discharging Time	:	2.5 hours (approx.) at 2A (The discharging time may vary for different devices)
Operation Temperature	:	5°C to 35°C

GP Batteries

Product Specification

Model no.: **RP10AB**

Safety protection : 1) Over voltage protection
2) Under voltage protection
3) Over charging protection
4) Over discharging protection
5) Over current protection
6) Short circuit protection
7) Loop back protection

LED Indication : **Charging & Discharging the Portable PowerBank**

Table 1

Charging & Discharging Condition	LED Indicator
Charging	Last LED flashing
Discharging	Refer to battery status (Table 2)
Fully charged	All LEDs On

Press button to show battery status :

Table 2

Battery Strength	LED indicator
Good	Four LED on
Good to average	First Three LED on
Average	First Two LED on
Weak	One LED on
Very Weak	One LED Flash
No Power	No LED

Dimensions : 145 (L) x 75 (W) x 15.2 (H) mm +/-0.5mm

Weight : 230g +/- 10g (approx.)

Certification : CE, FCC, Rohs, UN38.3

Warranty Period : 12 months from ex-factory date