

External Drive Piezo Transducer- 41.PT51L120H-LF



■ PZ Transducer 12V L/W ABS RoHS

■ Colour - Black



General Specification

Model Number	41.PT51L120H-LF
Sound Pressure Level	70dBA min. (12VP-P Square wave, 30 cm, 5000 Hz)
Capacitance	15000 pF +/-30% at 120Hz
Max. Input Voltage	40 V p-p
Operating Temperature	-20 ~ +60°C
Terminal	Leadwire
Housing Material	ABS
Weight (g)	2

Dimension (mm)

