

# Piezo Buzzer - 41.P29L120A-LF



■ PZ Buzzer Single 12VDC L/W ABS RoHS

■ Colour - Black




## General Specification

Model Number	41.P29L120A-LF
Operating Voltage Range (VDC)	1.5 ~ 16
Rated Voltage (VDC)	12
Max. Rated Current * (mA)	15
Min. Sound Output* (dBA/ 30cm)	95
Frequency * (Hz)	3200 +/- 500
Tone Nature	Single
Operating Temperature (°C)	-20 ~ + 60
Terminal	Leadwire
Housing Material	ABS
Weight (g)	15

\* Value applying at rated voltage

## Dimension (mm)

TOP VIEW



SIDE VIEW

