

Material number	0 600 847 A70
EAN	3165140582636
Voltage	220 V
Blade cover	✓
Top seller	0.0



Technical data

Technical data

Motor power	420 W
Blade length	450 mm
Tooth opening	16 mm
No-load stroke rate	3.400 spm
Weight	2,6 kg

Noise/vibration information

Sound pressure level	75 dB(A)
Sound power level	95 dB(A)
Uncertainty K	2 dB

Sales information

Positioning

- Lightweight and powerful for convenient hedgecutting.

User benefit

- Effortless handling: lightweight hedgecutter, designed to reduce the strain on your arms and back.
- Convenience: a well-balanced tool with ergonomic handles to ensure a more comfortable working position.
- Outstanding performance: high-speed motor and 16 mm tooth opening give you the cutting power for small to medium-sized hedges.

Highlights

- Optimum balance and ergonomics for comfortable working in any position
- High-performance 420 W motor for powerful cutting
- Small outer dimensions for better handling