

Material number	0 600 8A5 270
EAN	3165140689106
Line spool F 016 800 351	✓
Top seller	0.0



Technical data

Technical data

Motor power	450 W
Cutting diameter (line)	27 cm
Height adjustment	80 – 115 cm
Cutting system	Line spool
Cutting speed	10.500 rpm
Spool	1,6 mm x 6 m
Weight	2,7 kg



Functions

Plant protector	✓
Vertical edge-cutting 90°	✓

Noise and vibration information (line version)

Sound pressure level	73 dB(A)
Sound power level	93 dB(A)
Uncertainty K	1 dB

Sales information

Positioning

- High performance cutting with hassle free automatic line feeding

User benefit

- Automatic line feed system minimises management of the line
- Go from trimming to edging mode in just one click
- One click height adjust

Highlights

- Fully adjustable secondary handle
- Compact and lightweight
- Advanced motor providing a quick, clean finish
- Comfortable trimming experience with softgrip handle
- Twin line for increased cutting performance