

0 600 878 M70 – ART 35

Material number	0 600 878 M70
EAN	3165140649599
Voltage	230 V
8 m line spool F 016 800 345	✓
Shoulder strap	✓
Top seller	0.0



Technical data

Technical data

Motor power	600 W
Cutting diameter (line)	35 cm
Cutting system	Line spool
Cutting speed	8.000 rpm
Weight	4,6 kg

Noise and vibration information (line version)

Sound pressure level	87 dB(A)
Sound power level	94 dB(A)
Uncertainty K	1.5 dB

Sales information

Positioning

- Ideal for cutting high and hard grass, meadows, wild corners of the garden

User benefit

- Stable shaft and protection: withstands being dropped on hard surfaces and other forms of careless handling
- Light: easy to handle and transport
- Ergonomic hand grips: for effortless tool guidance

Highlights

- High motor performance: Efficient motor delivering similar work performance of models with higher power
- Easy to manoeuvre: good weight distribution and shoulder belt

