

Material number	0 600 803 370
EAN	3165140465373
Voltage	230.0 V
53 l collection box	✓
Practical plunger	✓
Top seller	0.0



## Technical data

### Technical data

Cutting system	“Turbine-Cut System”
Motor power	2.500 W
Cutting capacity, max. diameter	45 mm
Material throughput, approx.	230 kg/h
Cutting speed	41 rpm
Torque, approx.	650 Nm
Weight	30,5 kg
Collection box	53 l



### Functions

Automatic feed	✓
Collection box	✓

### Noise/vibration information

Sound pressure level	82 dB(A)
Sound power level	90 dB(A)
Uncertainty K	2 dB

## Sales information

---

### Positioning

- Versatile multi-purpose shredder.

### User benefit

- Universal: the new “Turbine-Cut System” guarantees extremely fast material throughput from greenery to hard wood, avoiding any blockages.
- Top performance: powerful shredders delivering up to 230 kg/h material throughput and 45 mm cutting capacity.
- Convenient: removable hopper gives 30% storage space reduction compared to predecessor – only 67 cm height when stored.

### Highlights

- Automatic feed and low noise levels for extremely convenient shredding
- Cutting capacity of up to 45 mm for powerful shredding
- Practical collection box. 53-litre capacity for easier collection of the shredded material
- Removable hopper for easy filling and convenient shredding
- Shielded cutting mechanism for greater user safety
- “Turbine-Cut System”. Innovative cutting system with motor power of 2500 watts
- Safety function of the collection box. The tool only works when the collection box has been inserted