



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™



CRIMPER 1600 OPEN BARREL AWG 30-18

Open Barrel Contact Pin Crimper

Cat No: PA1645

UPC No: 769328100754

Description

- Professional crimping tool for open-barrel box and round connector contacts with a wire range of 30-18 AWG (0.05-.75 mm²)
- Precision fixed dual-plate dies for crimp accuracy
- Crimps non-insulated terminal lugs, cable lugs and parallel and serial splices or F-Type
- Works with Molex, Waldom & Leoco-type connectors
- Durable steel construction for long life
- Rubber-embedded ergonomic handles for low-effort operation

Specifications

- Application : For Open-Barrel Box And Round Connector Contacts With A Wire Range Of 30-18 AWG (0.050 - 0.750 SQ-MM)
- Crimping Range : Small: 30-24 AWG (0.050 - 0.200 SQ-MM), Medium: 22-18 AWG (0.340 - 0.750 SQ-MM)
- Handle Type : Rubber Embedded Ergonomic
- Material : Durable Steel
- Type : Open Barrel Contact Pin
- Weight : 14.000 OZ (400.000 GM)