

Technical Specification

| Part No. | HDMI0102SV2 | HDMI0104SV2 | HDMI0108SV2 |
|----------------------|--|---------------------------------|---------------------------------|
| Input | HDMI×1(Type A, 19 pin, female) | | |
| Output | HDMI×2(Type A, 19 pin, female) | HDMI×4(Type A, 19 pin, female) | HDMI×8(Type A, 19 pin, female) |
| Input cable length | ≤5m(AWG26 HDMI cable support HDMI2.0) | | |
| Output cable length | ≤5m(AWG26 HDMI cable support HDMI2.0) | | |
| Video support | 480i@60Hz、480p@60Hz、 576i@50Hz、576p@50Hz、 720p@50/60Hz、1080i@50/60Hz、 1080p@50/60Hz、4K×2K@24/25/30/60Hz | | |
| Audio format | Support standard audio and DSD (Direct Stream Digital) and HD(HBR) audio | | |
| TMDS signal | 0.5~1.5Vp-p(TMDS) | | |
| DDC signal | 5Vp-p(TTL) | | |
| EDID DIP Switch | YES | | |
| HDCP | HDCP2.2 | | |
| | | | |
| Housing | Metal enclosure | | |
| Dimensions(L×W×H mm) | 96×59×16.8mm | 158×80×17mm | 262×81.6×23.5mm |
| Net weight | 100g | 200g | 453g |
| Power supply | 5V/1A | 5V/2A | 12V/3A |
| Power consumption | <5W | <8W | <20W |
| Operation temperaure | 0~60° | | |
| Storage temperature | -20~70° | | |
| Relative humidity | 20-90% (no condensation) | | |