



## DMG-400

Order No.: 23.1550

**Price upon request**

### PRODUCTINFOS

#### Dynamic gooseneck microphone

- Excellent sound characteristics
- Balanced version
- Cardioid polar pattern
- M10 threaded part (length: 8 mm)
- For console and front mounting
- Total length: 385 mm

### TECHNICAL SPECIFICATIONS

#### DMG-400

Type	gooseneck microphone
Transmission method	cable
Polar pattern	cardioid
System	dynamic

**DMG-400**

Audio frequency range	150-12,000 Hz
Nominal impedance	500 $\Omega$
Sensitivity	2.2 mV/Pa
Admiss. ambient temp.	0-40 °C
Dimensions	Ø 28 mm x 385 mm
Weight	219 g
Connection	bare cable ends