



DMG-600

Order No.: 23.1560

Price upon request

PRODUCTINFOS

Dynamic gooseneck microphone

- Balanced version
- Cardioid polar pattern
- 3-pole XLR plug
- Total length: 565 mm

TECHNICAL SPECIFICATIONS

DMG-600

Type	gooseneck microphone
Transmission method	cable
Polar pattern	cardioid
System	dynamic
Audio frequency range	200-12,000 Hz
Nominal impedance	500 Ω

DMG-600

Sensitivity	2 mV/Pa
Admiss. ambient temp.	0-40 °C
Dimensions	Ø 21 mm x 565 mm
Weight	162 g
Connection	XLR