



HSE-130/SK

Order No.: 23.6400

Price upon request

PRODUCTINFOS

Ultra-light headband microphone

- Back electret microphone cartridge
- Omnidirectional polar pattern
- 3-pole mini XLR inline jack
- Cartridge arm of adjustable length
- Compatible with pocket transmitters TXS-...HSE with 3-pole mini XLR connection
- External power supply, e.g. via phantom power supply adapter EMA-1 or EMA-300P
- Microphone windshield

TECHNICAL SPECIFICATIONS

HSE-130/SK

Type	headband microphone
Transmission method	cable
Polar pattern	omnidir.

HSE-130/SK

System	back electret
Audio frequency range	20-20,000 Hz
Nominal impedance	2 k Ω
Sensitivity	7.9 mV/Pa
Max. sound pressure	130 dB
Power supply	DC 1.5-9 V
Admiss. ambient temp.	0-40 °C
Weight	17 g
Connection	3-pole mini XLR