



HSE-152/SK

Order No.: 23.4280

Price upon request

PRODUCTINFOS

Ultra-light headband microphone

Ultra-light headband microphone

- Cardioid polar pattern
- High-quality back electret cartridge
- 3-pole mini XLR connection
- Excellent feedback rejection
- Turning cartridge arm of adjustable length
- Drip ring (protects cartridge from moisture)
- Compatible with all pocket transmitters TXS-...HSE with 3-pole mini XLR connection
- External power supply, e.g. via phantom power supply adapter EMA-1 or EMA-300P Microphone
- windshield

The reliable HSE-150 is now also available with cardioid characteristic. Thus, the extensive list of features of the HSE-150 is now completed by a further important detail: excellent feedback rejection. This microphone also features a

high-quality back electret cartridge which provides an optimum sound. The extra lightweight and almost invisible ergonomic headband makes the HSE-152 a perfect tool for every vocal artist.

- Wide transmission range
- Excellent feedback rejection
- Very comfortable to wear
- Stable positioning
- Turning cartridge arm of adjustable length
- Drip ring (protects cartridge from moisture)
- Compatible with all pocket transmitters TXS-...HSE with 3-pole mini XLR connection
- External power supply, e.g. via phantom power supply adapter EMA-1, EMA-2, EMA-40 or EMA-300P
- Microphone windshield

TECHNICAL SPECIFICATIONS

HSE-152/SK

| | |
|-----------------------|---------------------|
| Type | headband microphone |
| Transmission method | cable |
| Polar pattern | cardioid |
| System | back electret |
| Audio frequency range | 20-20,000 Hz |
| Nominal impedance | 1.5 k Ω |
| Sensitivity | 1.8 mV/Pa |
| Max. sound pressure | 130 dB |
| Power supply | DC 1.5-9 V |
| Admiss. ambient temp. | 0-40 °C |
| Weight | 7 g |
| Connection | 3-pole mini XLR |