



Quality Products. Service Excellence.

Knockdown 2-Post Aluminum Contractor Rack *RB-2PA Series*

1,500 lbs Weight Capacity



RACK BASICS®



Features

- Constructed of 5052H32 Aluminum rails.
- 45U - 83.12" Overall Height.
- 19" EIA-310-D compliant 12-24 double-tapped rails.
- Numbered rail markings.
- Side ganging and accessory mounting holes.
- Knockdown self-squaring design ships unassembled for easy handling and shipping protection.
- Includes starter pack of mounting hardware.
- Finished in textured black powder paint.
- Load rated to 1,500 lbs (680 kg) of equipment load capacity.
- RoHS Compliant.

Part of the Rack Basics® line of economy rack solutions.

Gallery



Accessories

- Universal Rack Shelf
- Two Post Mounting Adjustable Shelf
- Rack Panels
- Two Post Centered Shelf
- Two Post Mounting Deep Channel Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- 12-24 Mounting Hardware
- Outlet Strips
- Light Duty Caster Set for Open Frame Rack
- Rack and Cabinet Baying/Ganging/Joining Kit
- Vertical Rack Cable Manager with Door
- Vertical Finger Cable Manager with Door
- Top Wire Management
- Top Cable Chimney
- Two-Post Extension Support Bracket
- Horizontal Ring Cable Manager
- Horizontal Finger Cable Manager
- Grounding
- Rack Isolation Kit
- Bolt Down Kit

Old Design (Available while supplies last)

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Depth		Height	Width
RB-2PA45	84.02	20.20	13.54	45U	78.75	19.00

New Design

Part No.	Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
		Height	Width	Depth		Height	Width
Black	Natural Finish						
RB-2PA1945BK	RB-2PA1945NF	84.02	20.20	15.00	45U	78.75	19.00
RB-2PA2345BK	RB-2PA2345NF	84.02	21.40	15.00	45U	78.75	23.00

Tags: Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, Two-Post Rack *Data subject to change without notice*

© 2018. Hammond Manufacturing Ltd. All rights reserved.