



Description:

Cost effective 5" ceiling loudspeaker offering full range audio delivered utilising a dual cone driver, the loudspeaker is ideally suited for general background music and speech reinforcement. The loudspeaker is simple to install using the spring clips and a template is supplied for convenience.

Features:

- Dual cone driver for extended upper frequency response
- Multiple power taps
- Low profile design blends into environments
- ABS baffle with metal grille
- Spring clip mounting for easy installation
- Supplied with template to aid installation

Specifications:

- Power taps @ 100V: 1.5W, 3W, 6W
- Power taps @ 70V: 0.75W, 1.5W, 3W
- Impedance: 1.7K?, 3.3K?, 6.7K?
- Sensitivity (1W/1m): 89dB (± 3 dB)
- Maximum SPL (Rated W/1m): 96dB
- Frequency response: 80Hz-18kHz
- Drivers: 5" full range dual cone
- Connections: Flying leads
- Cutout: 145mm \emptyset
- Dimensions: 80 x 170mm \emptyset
- Weight: 0.75kg