

CR-S060VDC1R



Products → Low Voltage Products and Systems → Control Products → Electronic Relays and Controls
→ Interface Relays and Optocouplers

General Information

Extended Product Type:	CR-S060VDC1R
Product ID:	1SVR405501R5010
EAN:	4013614499166
Catalog Description:	CR-S060VDC1R Pluggable interface relay 1c/o, A1-A2=60VDC, Output=6 A/250VAC
Long Description:	CR-S060VDC1R Pluggable interface relay 1c/o, A1-A2=60VDC, Output=6 A/250VAC

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85364900

Popular Downloads

Data Sheet, Technical Information:	2CDC117022D0201
Instructions and Manuals:	2CDC117022D0201

Dimensions

Product Net Width:	5 mm
Product Net Height:	15 mm
Product Net Depth / Length:	28 mm
Product Net Weight:	0.005 kg

Technical

Function:	Pluggable slim interface relay CR-S
Sub-Function:	Relay with standard contacts
Output:	1 c/o (SPDT) contact
Output Signal:	250 V / 6 A
Rated Control Supply Voltage (U_s):	60 V DC

Environmental

Ambient Air Temperature:	Operation -40 ... +85 °C Storage 0 ... +40 °C
RoHS Status:	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

CQC Certificate:	CQC_14002108002
-------------------------	-----------------

CSA Certificate:	CSA_262671-2785865
cUR Certificate:	cUR_E244330
Declaration of Conformity - CE:	No declaration needed
EAC Certificate:	EAC_RU_C-PL.ME77.B.01873
Environmental Information:	1SAA981009-2403
Instructions and Manuals:	2CDC117022D0201
RoHS Information:	1SVD981001-4400
UR Certificate:	UR_E244330
VDE Certificate:	VDE_40039479

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	300 mm
Package Level 1 Height:	23.7 mm
Package Level 1 Depth / Length:	7.4 mm
Package Level 1 Gross Weight:	0.06 kg
Package Level 1 EAN:	4013614486494

Classifications

Object Classification Code:	K
E-nummer:	4001388
ETIM 4:	EC001437 - Switching relay
ETIM 5:	EC001437 - Switching relay
ETIM 6:	EC001437 - Switching relay
ETIM 7:	EC001437 - Switching relay
eClass:	7.0 27371601



