

# CR-S012/024VADC1SS



Products → Low Voltage Products and Systems → Control Products → Electronic Relays and Controls  
→ Interface Relays and Optocouplers

## General Information

<b>Extended Product Type:</b>	CR-S012/024VADC1SS
<b>Product ID:</b>	1SVR405521R3100
<b>EAN:</b>	4013614499203
<b>Catalog Description:</b>	CR-S012/024VADC1SS Socket 1c/o, A1-A2=12-24VAC/DC, 250VAC
<b>Long Description:</b>	CR-S012/024VADC1SS Socket 1c/o, A1-A2=12-24VAC/DC, 250VAC screw terminals

## Ordering

<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85369010
<b>Replacement Product ID (NEW):</b>	1SVR405521R3100 1SVR405510R3060

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	2CDC117022D0201
<b>Instructions and Manuals:</b>	2CDC117022D0201

## Dimensions

<b>Product Net Width:</b>	6.3 mm
<b>Product Net Height:</b>	76.4 mm
<b>Product Net Depth / Length:</b>	88.5 mm
<b>Product Net Weight:</b>	0.025 kg

## Technical

<b>Function:</b>	Accessory for interface relays CR-S
<b>Sub-Function:</b>	Socket
<b>Rated Control Supply Voltage (U<sub>s</sub>):</b>	12 ... 24 V AC/DC
<b>Terminal Type:</b>	Screw Terminals

## Environmental

<b>Ambient Air Temperature:</b>	Operation -40 ... +70 °C Storage 0 ... +40 °C
<b>RoHS Status:</b>	Following EU Directive 2011/65/EU

## Technical UL/CSA

<b>Connecting Capacity UL/CSA:</b>	Flexible 14 AWG Rigid 14 AWG
------------------------------------	---------------------------------

<b>Tightening Torque UL/CSA:</b>	4.42 in·lb
----------------------------------	------------

## Certificates and Declarations (Document Number)

<b>CSA Certificate:</b>	CSA_262671-2785566
-------------------------	--------------------

<b>cURus Certificate:</b>	cURus508_E244328
---------------------------	------------------

<b>Declaration of Conformity - CE:</b>	1SVD982017-0001
--	-----------------

<b>EAC Certificate:</b>	EAC_RU_C-PL.ME77.B.01873
-------------------------	--------------------------

<b>Environmental Information:</b>	1SAA981009-2403
-----------------------------------	-----------------

<b>Instructions and Manuals:</b>	2CDC117022D0201
----------------------------------	-----------------

<b>RoHS Information:</b>	1SVD982017-0001
--------------------------	-----------------

<b>VDE Certificate:</b>	VDE_40039479
-------------------------	--------------

## Container Information

<b>Package Level 1 Units:</b>	10 piece
-------------------------------	----------

<b>Package Level 1 Width:</b>	93 mm
-------------------------------	-------

<b>Package Level 1 Height:</b>	81 mm
--------------------------------	-------

<b>Package Level 1 Depth / Length:</b>	66 mm
--	-------

<b>Package Level 1 Gross Weight:</b>	0.26 kg
--------------------------------------	---------

<b>Package Level 1 EAN:</b>	4013614486333
-----------------------------	---------------

## Classifications

<b>Object Classification Code:</b>	K
------------------------------------	---

<b>E-nummer:</b>	4001392
------------------	---------

<b>ETIM 4:</b>	EC001456 - Relay socket
----------------	-------------------------

<b>ETIM 5:</b>	EC001456 - Relay socket
----------------	-------------------------

<b>ETIM 6:</b>	EC001456 - Relay socket
----------------	-------------------------

<b>ETIM 7:</b>	EC001456 - Relay socket
----------------	-------------------------

<b>eClass:</b>	7.0 27371603
----------------	--------------

<b>UNSPSC:</b>	39121516
----------------	----------

