

24120

## Speaker wall mount




### Product variant

24120-000-55 - black

### Data

<b>Adjustment</b>	gradual in 11 settings
<b>Angle of inclination</b>	0° to 22°
<b>Material</b>	steel
<b>Max. load capacity</b>	50 kg
<b>Mounting</b>	attaches to walls
<b>Mounting bolt</b>	straddling bearing-anchors diameter 35 to 37 mm x 85 mm
<b>Special features</b>	very flexible; patented straddling bearing-anchors; guarantee effective clamping of speaker in any position; resonance-optimised construction
<b>Swivel</b>	180 °
<b>Type</b>	black
<b>Wall plate</b>	580 x 140 mm
<b>Wall-to-bolt clearance</b>	20 mm
<b>Weight</b>	5.76 kg



The swivelling and tiltable wall mount holds your speaker at the angle you want. The mount has 11 different tilt settings moving through 22°. The swivel is adjustable to any angle. The patented expanding mandrel for loud speakers with cabinet interiors of diameter from 35 to 37 mm is tightened with a key for a non-wobble and low-resonance speaker fit.