

**Crimping tool  
HTF SUB-D**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Crimping tools for SUB-D contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

**General ordering data**

Type	HTF SUB-D
Order No.	<a href="#">9013260000</a>
Version	Crimping tool, Crimping tool for contacts, 28AWG, 20AWG, FoderBcrimp
GTIN (EAN)	4008190056896
Qty.	1 pc(s).

**Data sheet**

**Crimping tool  
HTF SUB-D**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Weight	438 g	Net weight	440.98 g

**Technical data**

Version	Mechanical, without interchangeable inserts
---------	---

**Description of contact**

Type of contact	SUB-D	Crimping range, min.	28 AWG
Crimping range, max.	20 AWG		

**tool data crimping**

Crimping profile 1, min.	28 AWG	Crimping type/profile	FoderBcrimp
Crimping profile 1, max.	24 AWG	Crimping profile 2, min.	22 AWG
Crimping profile 2, max.	20 AWG		

**Classifications**

ETIM 3.0	EC000168	ETIM 4.0	EC000168
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-03-01
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

**Data sheet**

**Crimping tool  
HTF SUB-D**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

