

Screwty M12f KO o. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The Screwty® attachment is suitable for customisable M12 round plug-in connectors, with an outside dimension of the knurled nut of 19.8 ± 0.3 mm. The tightening torque is 0.8-1.2 Nm.

General ordering data

Type	Screwty M12f KO o. SD
Order No.	1900120000
Version	Tools, Cable gland tool for M12 connectors
GTIN (EAN)	4032248409976
Qty.	1 pc(s).

Screwty M12f KO o. SD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 18 g

Classifications

ETIM 3.0	EC000174	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000149
eClass 6.2	21-04-01-90	eClass 7.1	21-04-01-90
eClass 8.1	21-04-01-90	eClass 9.0	21-04-01-90
eClass 9.1	21-01-90-90		

Approvals

ROHS Conform

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)
[CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)