

# LED LENSER® P3BM

This palm-sized power torch is only 96mm long but sends a bright white LED beam up to 31 metres away – easily enough for most near and some far-distance lighting needs. So small that it can be put in a pocket or attached to a key-ring it is a real illumination powerhouse, with easy-slide single-hand Speed Focus from flood to spot, and a slightly over-size lamp head for increased range. The quality of light is exceptional as the P3BM uses innovative Blue Moon Focus technology to separate out the blue light, pushing it to the edges to leave a strong central core of captivating white light. Unlike conventional bulbs, LEDs can last up to 50,000 hours, which means the only thing likely to need changing at some point is the single AAA battery (supplied). As that battery is inside a body made from ultra-light, high-strength aluminium, with energy-efficient inner gold plated contacts to aid conductivity, it is likely this torch will give dependable service for years to come.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Slim, pocket torch with handy key-ring attachment
- Energy efficient LED light-chip
- State-of-the-art, reliable German engineering
- Blue Moon Focus System™ delivers a brighter, whiter beam of light
- Robust, yet lightweight aircraft-grade aluminium housing
- Speed Focus™ enables smooth single-handed beam focusing
- Pocket clip – simple, safe attachment
- Superior rear tail cap switch
- Water and dust resistant. IPX54

## Technical Information

Size: 96 x 20mm Ø

Power: 16 lumens

Run Time: up to 7 hours

Beam Distance: up to 31m

Weight: 35 grams

Supplied with : Wrist-strap, belt/storage pouch and Duracell® battery (1xAAA)

Code	Colour	Packaging	Barcode
8403	Black	Gift Box	4029113840309
8403TP	Black	Test-It	4029113860307
8403GTP	Titanium	Test-It	4029113860406