

Product data sheet

Characteristics

XZCPV11V12L10

pre-wired connectors XZ - straight female - M12 -
5 pins - cable PVC 10m

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 24.98 USD



Main

Accessory / separate part category	Cabling accessory
Accessory / separate part type	Pre-wired connectors
Series name	General purpose

Complementary

Electrical connection	M12, 5 pins straight female connector
Cable connector fixing	Screw-on
Collar material	Metal
Status LED	Without
Cable length	32.81 ft (10 m)
Cable outer diameter	0.2 in (5.2 mm)
Cable composition	5 x 0.34 mm ²
Wire insulation material	PVC
System Voltage	60 V AC 75 V DC
Line Rated Current	3 A
Contact resistance	5000 μOhm
Insulating resistance	1 GΩ
Product weight	0.79 lb(US) (0.36 kg)

Environment

IP degree of protection	IP65 IP67
Product certifications	CULus
Ambient air temperature for operation	-13...176 °F (-25...80 °C) (static)
Ambient air temperature for storage	-13...176 °F (-25...80 °C)

Ordering and shipping details

Category	22483 - MACHINE CABLES
Discount Schedule	DS3

GTIN	003389119621526
Nbr. of units in pkg.	1
Package weight(Lbs)	0.90000000000000002
Returnability	N
Country of origin	CZ

Contractual warranty

Warranty period	18 months
-----------------	-----------