

## Audio

Speakers: Yes

## Basic

Aspect Ratio: 21:9  
Backlight Technology: LED  
Brand Name: LG  
Brightness: 300 cd/m<sup>2</sup>  
Built-in Devices: Speaker  
Colour Support: 16.7 Million Colours  
Colour: Black  
Silver  
Contrast Ratio: 1,000:1  
DisplayPort: Yes  
Environmental Certification: ErP  
TÜV  
Environmentally Friendly: Yes  
HDMI: Yes  
Maximum Resolution: 2560 x 1080  
Number of Screens: 1  
Product Family: Ultrawide 650  
Product Type: LCD Monitor  
Response Time: 5 ms GTG  
Screen Mode: UW-UXGA  
Screen Size: 86.4 cm (34")  
Speakers: Yes  
VESA Mount Compatible: Yes

## Built-in Devices

Built-in Devices: Speaker

## General Information

Brand Name: LG  
Manufacturer Part Number: 34WK650-W  
Manufacturer Website Address: <http://www.lge.co.uk>  
Manufacturer: LG Electronics  
Product Line: Ultrawide  
Product Model: 34WK650-W  
Product Name: Ultrawide 34WK650-W Widescreen LCD Monitor  
Product Series: 650  
Product Type: LCD Monitor

## Interfaces/Ports

DisplayPort: Yes  
HDMI: Yes

## Miscellaneous

Environmental Certification: ErP  
TÜV  
Environmentally Friendly: Yes

## Physical Characteristics

Colour: Black  
Silver  
Depth with Stand: 231.14 mm  
Depth: 231.1 mm  
Height with Stand: 571.50 mm  
Height: 370.8 mm  
VESA Mount Compatible: Yes  
Weight (Approximate): 5.90 kg  
Weight with Stand (Approximate): 7.60 kg  
Width with Stand: 825.50 mm  
Width: 825.5 mm

## Power Description

Off-Mode Power Consumption: 300 mW  
Operating Power Consumption: 42 W  
Standby Power Consumption: 500 mW

## Technical Information

Aspect Ratio: 21:9  
Backlight Technology: LED  
Number of Screens: 1

Pixel Pitch: 0.31 mm  
Response Time: 5 ms GTG  
Screen Mode: UW-UXGA  
Screen Size: 86.4 cm (34")

**Video**

Brightness: 300 cd/m<sup>2</sup>  
Color Gamut: 99% CIE 1931  
Colour Support: 16.7 Million Colours  
Contrast Ratio: 1,000:1  
Maximum Resolution: 2560 x 1080  
Tearing Prevention Technology: FreeSync