

# PRO-SIGNAL



PSG3031

HDMI SWITCH 2 PORT BI-DIRECTIONAL

## IMPORTANT SAFETY INFORMATION

Please read these instructions carefully before use and retain for future reference.

## OVERVIEW

- This device switches two HD sources to any one HD display or projector.
- Also it can distribute one HD source to two HD displays or projectors.

## WHAT'S IN THE BOX

- Main unit.
- User's Manual.

## INSTALLATION

- Please make sure all devices you wish to connect have been powered off.
- Connect the source device to the converter using appropriate HDMI cable.
- Connect the HDMI output to the displays.
- Two input sources to one output display or one input device to two output displays can be connected.
- There is no requirement for power to this device but consequently a maximum total cable length of 5m between source and display is recommended or quality may be reduced.
- Power on the source and receiving devices.
- When the button is pressed the switched active HDMI port is indicated by the LED.

## SPECIFICATIONS

Operating environment	0-40° / Storage -10 to 55°, Humidity up to 90%
Power supply	Power free
Power consumption (max)	15mA
HDMI Input	1080p plug and play
HDMI Specification	V1.0, V1.1, V1.2 and V1.3
Dimensions	42 x 50 x 25mm
Weight	35g



### INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Made in China. PR2 9PP  
Man Rev 1.0