

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Combination Starter
Range of product	S
Control circuit	Separate control circuit

### Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Poles description	3P
Motor power hp	5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases
System Voltage	600 V AC
Control type	No control units
Local signalling	No indicator
Auxiliary contact composition	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnecter device type	Fusible disconnect switch, Type H Fuse, 30 A
NEMA size	0

### Environment

NEMA degree of protection	NEMA 1 painted sheet steel and with external reset
---------------------------	--

### Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
GTIN	00785901748243
Nbr. of units in pkg.	1

---

Package weight(Lbs)	34.890000000000001
Returnability	Y
Country of origin	MX

---

**Offer Sustainability**

---

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---