

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0349674001](#)  
**Status:** **Active**  
**Overview:** [Mini50 Connection Systems](#)  
**Description:** Mini50 Sealed Receptacle, Single Row, with CPA, 4 Circuits, Polarization Option A, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Application Specification AS-34894-0001-001 \(PDF\)](#) [Product Literature \(PDF\)](#)  
[Packaging Specification PK-31301-898-001 \(PDF\)](#)

**General**

Product Family	Crimp Housings
Series	<a href="#">34967</a>
Application	Power, Sealed, Wire-to-Board
Comments	-40°C to +105°C operating temperature for tin terminals  -40°C to +125°C operating temperature for silver terminals
Overview	<a href="#">Mini50 Connection Systems</a>
Polarization	A
Product Literature Order No	987651-6273
Product Name	Mini50 Sealed
UPC	887191620381

**Physical**

Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	2.765/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C, -40°C to +125°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-34894-0001-001
Packaging Specification	PK-31301-898-001
Sales Drawing	349674000-000



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[34967 Series](#)

**Mates With**

Contact Molex for mating information.

**Use With**

CTX50 Sealed Receptacle Terminal  
[34905-2443](#) , [34905-2444](#)