



PA-900S

Order No.: 17.2080

Price upon request

PRODUCTINFOS

Mono PA power amplifier

- 1 x 120 W
- Silent operation due to fanless cooling concept
- 2-way tone control
- Switchable low cut filter
- Speaker outputs via screw terminals
- Feed-through output (link)
- Mains operation or 24 V emergency power operation
- 482 mm (19") rack installation with supplied mounting brackets

TECHNICAL SPECIFICATIONS

PA-900S

Channels	1
Power rating	120 W
Peak music power output (P_{MAX})	160 W
Output impedance	4 Ω , 70 V/ 100 V
Inputs	765 mV (line)
Frequency range	50-15,000 Hz, ± 3 dB
Equalizer bass	± 10 dB/100 Hz

PA-900S

Equalizer treble	± 10 dB/10 kHz
S/N ratio	> 80 dB
THD	< 0.5%
Power supply	~ 230 V/50 Hz/300 VA, DC 24 V/9 A
Mains voltage	~ 230 V
Mains frequency	50 Hz
Power consumption, operation	300 VA
Operating voltage (possible alternative)	DC 24 V
Power supply (possible alternative)	DC 9 A
Admiss. ambient temp.	0-40 °C
Dimensions	482 x 88 x 275 mm, 2 RS
Width	482 mm
Height	88 mm
Depth	275 mm
Rack spaces, RS	2
Weight	9.5 kg
Connections	1 x XLR, screw terminals (line in), 1 x XLR (line out), screw terminals (speakers)