



GNL-204

Order No.: 24.3700

Price upon request

PRODUCTINFOS

LED gooseneck light

- 4 white LEDs of high luminous intensity
- 12 V/60 mA
- Narrow beam angle
- BNC plug-in connector
- Length: 39 cm

Suitable for DC voltage and AC voltage due to built-in rectifier.

TECHNICAL SPECIFICATIONS

GNL-204

Type	LED gooseneck light
Type	4 white LEDs
Colour	black

GNL-204

Power supply	12 V/60 mA
Length	39 cm
Weight	73 g
Connections	BNC plug-in connector
Other features	narrow beam angle
Sales unit	1