



## GNL-404

Order No.: 24.3720

**Price upon request**

### PRODUCTINFOS

#### LED gooseneck light

- 4 white LEDs of high luminous intensity
- 12 V/60 mA
- Narrow beam angle
- XLR connector, 4 poles
- Length: 41 cm

Suitable for DC voltage and AC voltage due to built-in rectifier.

### TECHNICAL SPECIFICATIONS

#### GNL-404

Type	LED gooseneck light
Type	4 white LEDs
Colour	black

**GNL-404**

Power supply	12 V/60 mA
Length	41 cm
Weight	94 g
Connections	4-pole XLR
Other features	narrow beam angle
Sales unit	1