



VU-800/SW

Order No.: 20.2250

Price upon request

PRODUCTINFOS

Audio dB display

- 3-colour LED display with 40 LEDs
- Switchable display mode (dot display or bar graph display)
- Input level control for each channel
- 482 mm (19") rack installation, 1 RS
- Power is provided via enclosed plug-in power supply

TECHNICAL SPECIFICATIONS

VU-800/SW

Display	-45 dB to +12 dB
Admiss. ambient temp.	0-40 °C
Power supply	via encl. power supply
Dimensions	482 x 45 x 50 mm
Weight	795 g
Power supply	1 x low-voltage jack
Input, stereo	1 x RCA L/R
Output, stereo	1 x RCA L/R