



Quality Products. Service Excellence.

## Sloped Aluminum Consoles 1456 Series

### Key Features




- Aluminum cases 0.081" (2 mm) thick aluminum.
- Aluminum top panel sizes to 14" wide are 0.064" thick aluminum. Larger sizes are 0.081" thick.
- Sold pre-assembled with a textured blue case and a choice of a contempora grey (beige) or a black top panel.
- Comes with self adhesive rubber feet and required mounting hardware.
- Some models available with walnut sides - see series **1456CWW**
- Replacement screws **1421J6** (Pkg. of 6, 6-32 Philips head sheet metal screws).




### Photo Features




Vents on rear and bottom



All models have a blue base. Available with a beige or black top.



Shown unassembled



### Enclosures

Slope	Beige Top w/ Blue Case	Black Top w/ Blue Case	Width	Depth	Rear Height	Front Height
None	1456NEK4WHBU	1456NEK4BKBU	6.00	10.00	4.00	4.00
10 Degrees	1456FE1WHBU	1456FE1BKBU	6.50	5.50	2.50	1.50
10 Degrees	1456PH1WHBU	1456PH1BKBU	14.00	8.30	3.00	1.50
10 Degrees	1456RL1WHBU	1456RL1BKBU	17.00	11.30	3.50	1.50
10 Degrees	1456WL1WHBU	1456WL1BKBU	20.00	11.30	3.50	1.50
15 degrees	1456CE2WHBU	1456CE2BKBU	4.00	5.50	2.00	1.10
15 Degrees	1456FE2WHBU	1456FE2BKBU	6.50	5.50	2.00	1.10
15 Degrees	1456FH3WHBU	1456FH3BKBU	6.50	8.30	3.00	1.30

Slope	Beige Top w/ Blue Case	Black Top w/ Blue Case	Width	Depth	Rear Height	Front Height
15 Degrees	1456FH2WHBU	1456FH2BKBU	6.50	8.50	2.00	1.10
15 Degrees	1456KH3WHBU	1456KH3BKBU	10.00	8.30	3.00	1.30
15 Degrees	1456KL3WHBU	1456KL3BKBU	10.00	11.30	3.00	1.30
15 Degrees	1456PH3WHBU	1456PH3BKBU	14.00	8.30	3.00	1.30
15 Degrees	1456PL3WHBU	1456PL3BKBU	14.00	11.30	3.00	1.30
15 Degrees	1456RH3WHBU	1456RH3BKBU	17.00	8.30	3.00	1.30
15 Degrees	1456RL3WHBU	1456RL3BKBU	17.00	11.30	3.00	1.30
15 Degrees	1456WH3WHBU	1456WH3BKBU	20.00	8.30	3.00	1.30
15 Degrees	1456WL3WHBU	1456WL3BKBU	20.00	11.30	3.00	1.30
30 Degrees	1456CE3WHBU	1456CE3BKBU	4.00	5.50	3.00	1.10
30 Degrees	1456FE3WHBU	1456FE3BKBU	6.50	5.50	3.00	1.10
30 Degrees	1456FG4WHBU	1456FG4BKBU	6.50	7.20	4.00	1.10
30 Degrees	1456KE3WHBU	1456KE3BKBU	10.00	5.50	3.00	1.10
30 Degrees	1456KG4WHBU	1456KG4BKBU	10.00	7.20	4.00	1.10
30 Degrees	1456KK4WHBU	1456KK4BKBU	10.00	10.20	4.00	1.10
30 Degrees	1456PG4WHBU	1456PG4BKBU	14.00	7.25	4.00	1.10
30 Degrees	1456PK4WHBU	1456PK4BKBU	14.00	10.20	4.00	1.10
30 Degrees	1456RK4WHBU	1456RK4BKBU	17.00	10.20	4.00	1.10
30 Degrees	1456WK4WHBU	1456WK4BKBU	20.00	10.20	4.00	1.10

*Data subject to change without notice*

© 2018. Hammond Manufacturing Ltd. All rights reserved.