

Powerful and safe dust extractors for hazardous dust

The ATTIX 33 2M comes with more suction power, sealed dust system, semi automatic filter cleaning and several other user benefits - designed to meet the tough requirements in building & constructions and other industries when picking up hazardous M class dusts. This range represents a superior solution for professional customers looking for a reliable machine to protect workers health and safety.




To minimise dust exposure during disposal several dust bag options are available to match the specific need in the hazardous dust application. Also the washable PTFE long-life filter and the dual HEPA filter option minimises maintenance and reduces the overall service cost. A flow sensor with combined acoustic and LED warning monitors the filter and air flow to secure performance and filtration on the highest and most safe level. Easy handling and user-friendliness - also when it comes to transportation from one working site to another - are other valuable features for the ATTIX 33 2M dust extractor. All models offer flexible storage solutions for tools and accessories, so everything you need is at hand.



Picture shown may not represent model quoted

- Push&Clean™ - Semi-automatic filter cleaning system on selected models
- Dust class M certification
- PTFE long-life filter with non-stick membrane and minimum 99.9% filtration efficiency
- Flow sensor with combined acoustic and LED warning
- 30 litre container with steel castors and robust bumper
- MultiFit accessory system for the ultimate in task flexibility
- Rubber straps, tool box storage and optional trolley handle for convenient storage and transport
- Optional motor cooling filter, exhaust air collector and long-life filter bag

• Standard equipment



Included accessories	Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
Filter					
 FILTER ELEMENT Ø140X75 H-CLASS/HEPA	107413555	0			
 FLAT FILTER PTFE M-CLASS 1 PCS	107413540	0	•	•	•
System 32 Hose Vacuum Cleaner					
HOSE Ø32X4000MM AS RED	107413543	0	•	•	•
System 36 Hose Vacuum Cleaner					
 HOSE Ø36X4000 MM AS RED	107413544	0			
System 36 Tube					



Powerful and safe dust extractors for hazardous dust

Included accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	CURVED HAND TUBE Ø36MM SS	46691	0	•	•	•
	EXTENSION TUBE D36 3X350 MM SS	107416995	0			
	TOOL ADAPTER D27 QUICKSYSTEM	302000535	0	•	•	•
System 36 Brush/Universal Nozzle						
	SUCTION BRUSH D36 BLACK	302002509	0			
	UNIVERSAL NOZZLE D36X115	14295	0			
System 36 Vac Floor Nozzle						
	FLOOR NOZZLE Ø36X300MM	302002331	0	•	•	•
	FLOOR NOZZLE Ø36X360MM WET/DRY	60356	0			
System 36 Crevice/Cone Nozzle						
	CREVICE NOZZLE D36X200	29541	0	•	•	•
Filter Bag						
	FLEECE FILTER BAG 5 PCS ATTIX 33/44	107413547	0			
Disposal Bag						
	DISPOSAL BAG ATTIX 33/44 5 PCS	107417821	0			
Safety Filter Bag						
	SAFETY FILTER BAG 5 PCS ATTIX 33/44	107413549	0			
Other						

Powerful and safe dust extractors for hazardous dust

Included accessories	Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
 ADAPTER PLATE KIT	107413551	0			
 FLEXIBLE STRAP SET 2 PCS	107413553	0	•	•	•
 TROLLEY HANDLE KIT	107413552	0			

Model	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
Ref. no.	107412179	107412191	107412189

PRODUCT FEATURES

Softstart	•	•	•
Dual filter system			
Anti-static system	•	•	•
Motor speed control	•	•	•
Automatic On/Off-elec. tools	•	•	•
M-class hazardous dust approval	•	•	•
H-class hazardous dust approval			
Storage of accessories	•	•	•
Extra socket for tool	•	•	•
Hose and cable holder	•	•	•
Disposal bag 1 pcs			
Fleece filter bag 1 pcs	•	•	•
Safety filter bag 1 pcs			









Technical specifications	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
Power Pmax (W)	1400	1200	1400
Power Piec (W)	1200	1000	1200
Mains connection (V/~/Hz/A)	230/1/50-60/16	110/1/50-60/16	230/1/50-60/13
Airflow rate (l/min.)	4500	4200	4500
Vacuum (mbar/kPa)	250/25	230/23	250/25
Working sound level (dB(A))	60	60	60
El cable (m)	7.5	7.5	7.5



Powerful and safe dust extractors for hazardous dust

Technical specifications	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
Container volume (l-max)	30	30	30
Filter cleaning system	Push&Clean	Push&Clean	Push&Clean
Main filter type	PTFE M-class	PTFE M-class	PTFE M-class
Length x width x height (mm)	565x385x520	565x385x520	565x385x520
Weight (kg)	14.5	14.5	14.5

● Standard equipment, ○ Supplementary accessories, □ Mountable equipment

Accessories	Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
System 36 Crevice/Cone Nozzle					
 CREVICE NOZZLE D36X200	29541	0	●	●	●
 CREVICE NOZZLE Ø36X300 PP	6084	0	○	○	○
CREVICE NOZZLE Ø 36X15X920 ST/CR	17836	0	○	○	○
 DIA. TUBE NOZZLE Ø36x190 MM GREY RUBBER	5067	0	○	○	○
FLAT NOZZLE Ø36MM RUBBER	40456	0	○	○	○
System 50 Tube					
 ADAPTER Ø50-36MMX125	40452	0			
 CURVED ALU EXT.TUBE Ø50X1000	15335	0			
 CURVED HAND TUBE Ø50-36MM	15341	0			
 ELBOW 90 Ø 50MM	5089	0	○	○	○
 SUCTION TUBE Ø50 2X525MM PVC	5152	0			














Powerful and safe dust extractors for hazardous dust

Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
System 36 Brush/Universal Nozzle						
	BRUSH NOZZLE Ø36X70	5146	0	○	○	○
	BRUSH NOZZLE Ø36X230 PP/PA	6086	0	○	○	○
	OVAL BRUSH NOZZLE Ø36MM	40455	0	○	○	○
	RADIATOR BRUSH NOZZLE Ø36X420	5144	0	○	○	○
	SUCTION BRUSH D36 BLACK	302002509	0	○	○	○
	TURBINE HAND BRUSH NOZZLE Ø36X150MM	41275	0	○	○	○
	UNIV NOZZLE Ø36X150 ALU	5145	0	○	○	○
	UNIVERSAL NOZZLE D36X115	14295	0	○	○	○
System 36 Vac Floor Nozzle						
	COMBI NOZZLE Ø36X260MM	302002365	0	○	○	○
	COMBI NOZZLE Ø36X260MM PP	302000477	0	○	○	○
	ELECTRIC TURBINE BRUSH Ø36X305MM 230V	11664	0	○	○	○
	FLOOR NOZZLE COMBI Ø36X270MM	107417892	0	○	○	○













Powerful and safe dust extractors for hazardous dust

Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	FLOOR NOZZLE D36x300MM W/D KIT	107402706	0	○	○	○
	FLOOR NOZZLE D36x400MM W/D	302003666	0	○	○	○
	FLOOR NOZZLE Ø36x300MM	302002331	0	●	●	●
	FLOOR NOZZLE Ø36x330 ALU	5147	0	○	○	○
	FLOOR NOZZLE Ø36x360MM WET/DRY	60356	0	○	○	○
	FLOOR NOZZLE Ø36x400 SPECIAL WET/DRY	5149	0	○	○	○
	NOZZLE ALU. 450XØ36MM DRY	15348	0	○	○	○
	NOZZLE ALU. 450XØ36MM WET	15349	0	○	○	○
	OFFICE COMBI NOZZLE Ø36x300MM	302000259	0	○	○	○
	TURBINE BRUSH NOZZLE 300XØ36MM	54118	0	○	○	○
	WATER SUCTION NOZZLE Ø36X300	7270	0	○	○	○
System 50 Brush/Universal Nozzle						
	COARSE DIRT NOZZLE Ø50X175 PP	5153	0			
	COARSE DIRT NOZZLE Ø50X200MM ALU	41100	0			

Powerful and safe dust extractors for hazardous dust












Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	ROUND BRUSH NOZZLE Ø50MM	40458	0			
System 38 Hose Vacuum Cleaner						
	HOSE D38X5000 AS	107401368	0	○	○	○
	HOSE HEAT RES. 36X4000 FOR	6070	0	○	○	○
	UNI. SUCTION HOSE Ø38X4000MM EVA	302002796	0	○	○	○
	UNIV HOSE Ø36-38X4000MM EVA	15365	0	○	○	○
System 50 Vac Floor Nozzle						
	FLOOR NOZZLE ALU. 500XØ50MM DRY	15343	0			
	FLOOR NOZZLE Ø50x450 WET/DRY ADJ	302002880	0			
	FLOOR NOZZLE Ø50X350 PVC	6077	0			
	NOZZLE ALU. 500XØ50MM WET	15344	0			
Vacuum Accessory Set						
	ANIMAL CARE SET Ø27MM 4-PCS	6095	0	○	○	○
	BOILER SET Ø 36MM 4-PCS	60430	0	○	○	○

Powerful and safe dust extractors for hazardous dust







	Accessories	Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	CAR SET Ø36MM 3 PCS	63211	0	○	○	○
	CHIP SET Ø50MM 2-PCS	61681	0			
	HOME & OFFICE SET Ø36MM 5-PCS	63212	0	○	○	○
	HOSE SET Ø36MM 3 PCS	63210	0	○	○	○
	INDUSTR. FLOOR SET Ø36MM 4-PCS	63214	0	○	○	○
	INDUSTR. FLOOR SET Ø50MM 6-PCS	63216	0			
	INDUSTRIAL SET 38	302002881	0	○	○	○
	OVEN CLEANING SET 3 PCS	14341	0	○	○	○
	PIPE CLEANING SET Ø 38MM 4-PCS	63215	0	○	○	○
	STANDARD VAC SET Ø50MM 3-PCS	6085	0			
	TRADE AND IND. SET Ø36MM 5-PCS	63213	0	○	○	○
	WATER VACUUM SET Ø36MM 3- PCS	7727	0	○	○	○



Powerful and safe dust extractors for hazardous dust









Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	WORKSHOP HOSE KIT AS SYSTEM 36 6 PCS	107413546	0	○	○	○
	WORKSHOP HOSE KIT SYSTEM 36 5-PCS	107413545	0	○	○	○
	WORKSHOP KIT BASIC D36MM 4PCS	107401367	0	○	○	○
	WORKSHOP SET Ø36MM 6-PCS	302000927	0	○	○	○
System 27 Brush/Universal Nozzle						
	BRUSH CURRY COMB Ø 27MM	6093	0	○	○	○
	CURRY COMB Ø27MM	6092	0	○	○	○
	SPIKED CURRY COMB Ø 27MM	6094	0	○	○	○
System 50 Hose Vacuum Cleaner						
	AS HOSED50X4000MM	15815	0			
	CHIPS HOSE Ø50X4000MM	15182	0			
	HOSE HEAT RESIST. Ø 50X4000MM	11061	0			
	HOSE OIL RESISTANT D50X40	6468	0			
	METAL HOSE Ø50X4000MM	15013	0			

Powerful and safe dust extractors for hazardous dust

Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	UNI. HOSE Ø50X4000MM EVA/ABS	15358	0			
	UNIV HOSE Ø 50X1750MM	19930	0			
System 50 Crevice/Cone Nozzle						
	CREVICE NOZZLE Ø50X370 PE	7102	0			
	DIAGONAL TUBE NOZZLE Ø50 RUBBER	7868	0			
	FLAT NOZZLE RUBBER Ø 50MM	31244	0			
	ROUND NOZZLE Ø50MM RUBBER	19936	0			
System 38 Crevice/Cone Nozzle						
	CREVICE FLAT NOZZLE Ø38X240X65 MM	43535	0	○	○	○
	CREVICE NOZZLE Ø38x300 MM PP	302002890	0	○	○	○
	PIPE CLEAN NOZZLE Ø38 R120-200MM	8054	0	○	○	○
	TOOL ADAPTER 38/50 MM	302002884	0	○	○	○
System 27 Hose Vacuum Cleaner						
	HOSE D27X3500 AS WITH TOOL ADAPTER	107406091	0	○	○	○
	TOOL ADAPTER D27/36-24 AS	107404520	0	○	○	○












Powerful and safe dust extractors for hazardous dust

Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	UNIV HOSE Ø27X3500 WITH TOOL ADAPTER EVA	14289	0	○	○	○
System 32 Hose Vacuum Cleaner						
	AS HOSED32X5000MM WITH TOOL	30657	0	○	○	○
	COAXIAL SUCTION HOSE Ø32 SET	107400841	0	○	○	○
	HOSE Ø32X4000MM AS RED	107413543	0	●	●	●
	HOSE SLEEVE Ø32 PVC	14682	0	○	○	○
System 36 Hose Vacuum Cleaner						
	HOSE AS D36X4000MM	15311	0	○	○	○
	HOSE Ø36X4000 AS EVA	63209	0	○	○	○
	HOSE Ø36X4000 MM AS RED	107413544	0	○	○	○
	HOSE Ø36X5000MM AS W COUPLING	302001682	0	○	○	○
	SUCTION HOSE Ø36X3500 HEAT/OIL-RESISTANT	302001677	0	○	○	○
	UNI. HOSE Ø36X3000MM EVA	15805	0	○	○	○
	UNI. HOSE Ø36X3000MM W COUPLING EVA	46948	0	○	○	○
	UNI. HOSE Ø36X4000MM EVA	25537	0	○	○	○
	UNIV HOSE WITH HAND TUBE D32X3500 CPL.	107409976	0	○	○	○
	UNIV HOSE WITH HAND TUBE Ø32X3000	302000473	0	○	○	○
System 38 Tube						
	CURVED HAND TUBE D38 MM SS	302002889	0	○	○	○
	EXTEN TUBE THERMAL INSULATE Ø38X2000MM	15339	0	○	○	○





Powerful and safe dust extractors for hazardous dust

Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	EXTEN TUBE THERMAL INSULATE Ø38X2500MM	15340	0	○	○	○
	EXTENSION TUBES R38 2X500 KIT	107402474	0	○	○	○
System 36 Tube						
	ADAPTER TUBE STRAIGHT AS Ø36MM	29457	0	○	○	○
	CURVED HAND TUBE D36MM ST/CR	302000528	0	○	○	○
	CURVED HAND TUBE Ø36MM SS	46691	0	●	●	●
	EXTENSION TUBE D36 2X500MM ALU	107400032	0	○	○	○
	EXTENSION TUBE D36 2X505MM ST/CR	302000529	0	○	○	○
	EXTENSION TUBE D36 2X515MM PLASTIC	40696	0	○	○	○
	EXTENSION TUBE D36 3X350 MM SS	107416995	0	○	○	○
	TELESCOPIC TUBE D36 575-930MM CR-ST	107402654	0	○	○	○
	TELESCOPIC TUBE Ø36X550-970 SS	47109	0	○	○	○
	TOOL ADAPTER D27 QUICKSYSTEM	302000535	0	●	●	●
	TOOL ADAPTER D27/35/38	60916	0	○	○	○
	TOOL ADAPTER WITH SUCTION REGULATION D32	107409977	0	○	○	○
Disposal Bag						

Powerful and safe dust extractors for hazardous dust

Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	DISPOSAL BAG ATTIX 33/44 5 PCS	107417821	0	○	○	○
	DISPOSAL BAG FOR FILTER ELEMENT	30082	0	○	○	○
Other						
	ADAPTER PLATE KIT	107413551	0	○	○	○
	FLEXIBLE STRAP SET 2 PCS	107413553	0	●	●	●
	SPARK EXTINGUISHER Ø50	34591	0	○	○	○
	STORAGE L-BOX KIT W. DUSTBAGS	107413554	0	○	○	○
	TROLLEY HANDLE KIT	107413552	0	○	○	○
System 38 Vac Floor Nozzle						
	FLOOR NOZZLE D38x400 WET AND DRY	302002798	0	○	○	○
	FLOOR NOZZLE Ø38x450 WET AND DRY ADJ	302002799	0	○	○	○
	OVEN NOZZLE 400X Ø 38MM	63380	0	○	○	○
Filter						
	FILTER ELEMENT Ø140X75 H-CLASS/HEPA	107413555	0	○	○	○

Powerful and safe dust extractors for hazardous dust

Accessories		Ref. no.	Min. required	ATTIX 33-2M PC 220-240V 50/60HZ EU	ATTIX 33-2M PC 110-120V 50/60HZ GB	ATTIX 33-2M PC 220-240V 50/60HZ GB
	FLAT FILTER PTFE M-CLASS 1 PCS	107413540	0	•	•	•
	HEPA FILTER COVER KIT	107413542	0	○	○	○
Special Filter						
	MOTOR COOLING AIR FILTER PET 1 PCS	107413541	0	○	○	○
Filter Bag						
	FLEECE FILTER BAG 5 PCS ATTIX 33/44	107413547	0	○	○	○
	LONG LIFE FILTER BAG 1 PCS ATTIX 33/44	107413556	0	○	○	○
Safety Filter Bag						
	SAFETY FILTER BAG 5 PCS ATTIX 33/44	107413549	0	○	○	○
Exhaust Air Collector						
	EXHAUST AIR ADAPTER KIT	107417865	0	○	○	○