

# Waterproof RJ45 Plug Cat6, STP




## Specifications

Connector Type	: RJ45 Plug
No. of Contacts	: 8P8C
No. of Ports	: 1Port
LAN Category	: Cat6
Contact Termination	: IDC
Connector Mounting	: Cable
Waterproof Rating	: IP67 (Immersed in 1m water for 30 minutes)
Current Rating	: 1.5A
Voltage Rating	: 125V
Contact Resistance	: 30mΩ Max. (Initial)
Dielectric Withstanding Voltage	: 750V AC for 1 minute
Insulation Resistance	: 500MΩ Min. measured by 500V DC

## Material Specifications

Sealing Nut	: PA 6.6, Black
Seal	: EPDM, Black
Screw Nut	: PPE, Black
Clamp Ring	: PC, Black
Gasket	: EPDM, Black

## Diagram



## Part Number Table

Description	Part Number
Waterproof RJ45 Cat6 STP Plug, 8P8C, 1Port, Cable	MC002818

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)

