

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [121040-0159](#)
Status: **Active**
Overview: [Brad® mPm® DIN Valve Connectors](#)
Description: [Brad® mPm® DIN Valve Connector](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	121040
IP Rating	IP67
Overview	Brad® mPm® DIN Valve Connectors
Product Name	mPm®
Type	Field Attachable Connector
UPC	883906580711

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	153.630/g
Orientation	90° Angle
Poles	N/A
Temperature Range - Operating	-25°C to +75°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	5A
Voltage - Maximum	250V AC/DC

Material Info

Old Part Number	E152N3N20011
-----------------	--------------

Reference - Drawing Numbers

Sales Drawing	E152XXXXXXXX
---------------	--------------



EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
 Not Reviewed
Low-Halogen Status
 Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

121040Series