

# GET FULLY EQUIPPED STORAGE DEALS



26" FOAM INLAYS  
Dimensions 543x445 mm

### FF1A100 - 81 Pieces

6700SM - 1/4" SOCKETS HEX 4-13 MM  
4 - 4.5 - 5 - 5.5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 MM

A6800DM - 1/4" LONG SOCKETS HEX 7-13 MM  
7-8-10-11-13 MM

6956 - 1/4" SPINNER

6961 - 1/4" EXTENSION 100 MM

6966 - 1/4" UNIVERSAL JOINT

7800SM - 1/2" SOCKETS HEX 10 - 34 MM  
10-11-13-14-15-16-17-18-19-20-21-24-27-30-32-34 MM

7805DM - 1/2" SOCKETS LONG 10 - 19 MM  
10-13-16-17-18-19 MM

7805SM - 1/2" SPARK PLUG 16 - 21 MM  
16-21 MM

8160-1/2 - 1/2" EXTENSION - 125 MM

8162-1/2 - 1/2" EXTENSION - 250 MM

8166-1/2 - 1/2" UNIVERSAL JOINT

8156-1/2 - 1/2" BREAKER BAR

7106S0080 - 1/2" sq 5/16 HEX BIT HOLDER

6973 - 1/4" sq 1/4 HEX BIT HOLDER

70S - 5/16" BITS - T45-T50-T55

6950RN - RATCHET 1/4", ROUND TYPE

8150RN-1/2 - RATCHET 1/2", ROUND TYPE

2058-BR - BIT RATCHET 1/4"

7809M - SOCKET DRIV 1/2" HEX 60 MM  
5-6-7-8-10-12-14-17 MM

7809M-5-180 - SOCKET DRIV 1/2" HEX5 100 MM

7809M-6-180 - SOCKET DRIV 1/2" HEX6 100 MM

7809M-7-100 - SOCKET DRIV 1/2" HEX7 100 MM

7809M-8-120 - SOCKET DRIV 1/2" HEX8 100 MM

7809M-10-140 - SOCKET DRIV 1/2" HEX10 100 MM

7809M-12-180 - SOCKET DRIV 1/2" HEX12 100 MM

7809TORX - SOCKET DRIV 1/2" TORX® 60 MM  
T30 - T40 - T45 - T50 - T55 - T60

7809TORX-T40-120 - SOCKET DRIV 1/2" TORX® T40 120 MM

7809TORX-T45-120 - SOCKET DRIV 1/2" TORX® T45 120 MM

7809TORX-T50-100 - SOCKET DRIV 1/2" TORX® T50 120 MM

7809TORX-T55-140 - SOCKET DRIV 1/2" TORX® T55 140 MM



26" FOAM INLAYS  
Dimensions 543x445 mm

### FF1A101 - 24 Pieces

111M - COMBINATION WRENCH  
8-9-10-11-12-13-14-15-16-17-18-19-21-22-24-27-32 MM

7224 - SLIP JOINT PLIER 250 MM

2101G-180IPS - SIDE CUTTER 180 MM

2628 G-180IPRU - COMB PLIER 180 MM

2800-180 - CIRCLIP PLIER 2800-180 MM

2900-180 - CIRCLIP PLIER 2900-180 MM

2890-180 - CIRCLIP PLIER 2890-180 MM

2990-180 - CIRCLIP PLIER 2990-180 MM



26" FOAM INLAYS  
Dimensions 543x445 mm

### FF1A102 - 82 Pieces

3734S/6 - COTTER PIN PUNCHES SET

59/S54B - 54 PCS BIT SET RETAIL

482-40 - RIVOIR HAMMER

B191.025.075 - SCREWDRIV STRAIGHT 2.5x0.4x75

B191.035.100 - SCREWDRIV STRAIGHT 3.5x0.6x100

B190.055.125 - SCREWDRIVER SLOTTED 5.5x1x125

B190.080.150 - SCREWDRIVER SLOTTED 8x1.6x150

B192.000.075 - SCREWDRIVER PH0x75

B192.001.100 - SCREWDRIVER PH1x100

B192.002.125 - SCREWDRIVER PH2x125

B194.010.075 - SCREWDRIVER TORX® T10x75

B194.020.100 - SCREWDRIVER TORX® T20x100

B194.030.150 - SCREWDRIVER TORX® T30x150

B194.040.150 - SCREWDRIVER TORX® T40x150

2957-300 - UNIVERSAL GRIP PLIER 300 MM

BE-9770-B - SCREWDR SET HEX 1.5-10 BULK

## Automotive Industry

1470K7BKFF9SD

### 188 pieces tool trolley with premium tools

- 26" 7 Drawers Tool Trolley
- Heavy duty double wall frame tool trolley with click/ detent closing system on slides
- Design ensures that drawers and slides operate even if the frame is damage

