

Product information

Job Site Radio with Bluetooth



DMR108

Battery Type	Lithium-ion
Body only machine	1
Battery Range	7.2 - 18 v
Frequency Range FM	87.5 - 108 Mhz
Frequency Range AM	522 - 1710 kHz
Speakers	2x89mmØ
Practical Output (7.2v)	0.5W x 2
Practical Output (10.8v)	1.2W x 2
Practical Output (14.4v)	2.2W x 2
Practical Output (18v)	3.5W x 2
Net weight	4.3 - 4.9 kg



STANDARD EQUIPMENT: AC power adaptor, x2 AA Batteries

- Equipped with Bluetooth class 2 to wirelessly connect your mobile device for playing music with a range up to 10m.
- Newly compatible with 10.8V CXT slide batteries
- IP64 rated dust and shower-proof construction
- Foldable antenna
- Soft grip carry handle swivels 90 degrees
- Elastomer bumpers protect against rough handling on a jobsite
- 2 speaker stereo system.
- Flat top surface to stably place mobile device
- AUX-IN jack allows for connection to personal audio players
- AC adaptor jack
- Digital display
- USB port allows for charging mobile device.

Details correct as of: 6-9-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com