


LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Thermocouple Extension & Compensating Cable PVC Insulated Flat Pair

- ◆ PVC insulated flat pair construction
- ◆ Conductors laid flat PVC insulated with overall PVC sheath
- ◆ All round general purpose cable, both waterproof and very flexible
- ◆ Thermocouple extension types for K, J, T & N
- ◆ Compensating types VX (KCB) & U (RCA) for types K & R/S Thermocouples respectively
- ◆ Stranded conductors available, either 7/0.2mm or 13/0.2mm
- ◆ Available in 10, 25, 50 & 100 metre lengths
- ◆ Tolerance Class 2
- ◆ Insulation rating -10°C to 105°C
- ◆ Colour code (cores & jacket) to IEC-584-3



T/C Type	Conductors	Cores	Jacket	Reel Length	Manufacturers Part No.
<u>Extension:</u>					
K	7/0.2mm	+Green/-White	Green	10m	WK-150/10M
K	7/0.2mm	+Green/-White	Green	50m	WK-150/50M
K	7/0.2mm	+Green/-White	Green	100m	WK-150
J	7/0.2mm	+Black/-White	Black	10m	WJ-200/10M
J	7/0.2mm	+Black/-White	Black	500m	WJ-200/50M
J	7/0.2mm	+Black/-White	Black	100m	WJ-200
T	7/0.2mm	+Brown/-White	Brown	50m	WT-200/50M
T	7/0.2mm	+Brown/-White	Brown	100m	WT-200 T
T	13/0.2mm	+Brown/-White	Brown	50m	WT-009/50M
N	7/0.2mm	+Pink/-White	Pink	10m	WN-001/10M
<u>Compensating:</u>					
VX (KCB)	7/0.2mm	+Green/-White	Green	25m	WV-100/25M
VX (KCB)	7/0.2mm	+Green/-White	Green	100m	WV-100/100M
VX (KCB)	13/0.2mm	+Green/-White	Green	100m	WV-009/100M
U (RCA)	13/0.2mm	+Orange/-White	Orange	100m	WU-100/100M

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com