



50" Android 7.0 Smart 4K Ultra HD LED TV with T2 HD

- 58" 4K Ultra HD widescreen LED TV
- Android 7.0 Smart TV with built-in Wi-Fi (Superfast intuitive user interface)
- Cello Play (Watch catch up TV moving back and forward through the EPG)
- T2 HD channels
- 3,840 x 2,160 screen resolution
- USB – play saved media files
- HDMI x 3 inputs for external devices & consoles
- Wall mountable (400mm x 400mm)

	EAN	5060062268133
General Feature	Model No.	C50SFS4K
	Panel(60Hz/120Hz/3D)	V500DJ6-QE1
	Destination Country	UK
	Screen Size	50 inch LED Panel(Approx. 127cm)
	Max. Resolution	UHD 3840 x 2160 4K
	Contrast Ratio (Typical)	3200:1
	Brightness(TYP cd/m2)	200
	Viewing Angle(L/R/U/D)	89/89/89/89(CR≥10)
	Cabinet Color	Piano Black
	Wall Mounting Support(Screw Size)	400 x 400mm(M6 x 10)

Reception	TV System	DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	Number of channel for storing	400 Digital

Sound	Bass	N/A
	Treble	N/A
	Balance	N/A
	Sound Mode	N/A
	Stereo System	N/A
	Audio Output	2 x 8W
	Speaker Distortion	<=7% Max
	Speaker Impedance	8ohm

Connectors Jack	RF Antenna	1
	HDMI	YES x 4 (ver2.0)
	CVBS	YES x 1 (mini jack)
	PC In	N/A
	Audio In	CVBS Audio x1
	Scart	N/A
	YPbPr	N/A
	Digital Audio out	YESx 1
	Earphone Out	YESx 1
	USB	YESx 2 (Multi Media & Wireless Mouse and Keyboard)
	CI	N/A
	RCA	YESx 1
	RJ45	YESx 1
	Micro SD card	YESx 1

Android	SOC	Amlogic 962X
	RAM	2GB DDR4
	GPU	
	Built-in Flash	8GB
	Wi-Fi	YESx 1
	OS	Android 7

Other Features	APS	DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Francais, Espanol, Portugese, Italian.
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES
	Wifi on Android	YES
	Hotel Mode	N/A

Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	85W
	KWh/annum	120kWh
	Max power Consumption	120W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	A

Accessories	QSG	YES x 1
	Remote Control	YES x 1
	Power Cable	YES x 1
	Warranty	YES x 1
	Battery	1.5V(AAA)x2

Dimension	Unit Dimension With Stand (W x D x H mm)	1128.2 x 286.2 x 706.9
	Unit Dimension Without Stand (W x D x H mm)	1128.2 x 89.5 x 653.9
	Weight of unit(kg)	10.8