



**65" Android 7.0 Smart 4K HDR LED TV with T2 HD**

- 65" 4K Ultra HD widescreen LED TV
- Android 7.0 Smart TV with built-in Wi-Fi (Superfast intuitive user interface)
- Cello Play (Watch catch up TV moving back and forward through the EPG)
- T2 HD channels
- 3,840 x 2,160 screen resolution
- USB – play saved media files
- HDMI x 4 inputs for external devices & consoles
- Wall mountable (800mm x 400mm)

	EAN	5060062268201
<b>General Feature</b>	Model No.	C65SFS4K
	Panel (60Hz/120Hz/3D)	T650QVN06.3
	Destination Country	UK
	Screen Size	65 inch LED Panel (Approx. 165cm)
	Max. Resolution	UHD 3840 x 2160 4K
	Contrast Ratio (Typical)	4500:1
	Brightness (TYP cd/m2)	200
	Viewing Angle ( L/R/U/D )	89/89/89/89 (CR≥10)
	Cabinet Color	Piano Black
	Wall Mounting Support (Screw Size)	600 x 300mm (M6 x 10)

<b>Reception</b>	TV System	DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	Number of channel for storing	400 Digital

<b>Sound</b>	Bass	N/A
	Treble	N/A
	Balance	N/A
	Sound Mode	N/A
	Stereo System	N/A
	Audio Output	2 x 8W
	Speaker Distortion	<=7% Max
	Speaker Impedance	8ohm

<b>Connectors Jack</b>	RF Antenna	1
	HDMI	YES x 4 (ver2.0)
	CVBS	YES x 1 (mini jack)
	PC In	N/A
	Audio In	CVBS Audio x1
	Scart	N/A
	YPbPr	N/A
	Digital Audio out	YES x 1
	Earphone Out	YES x 1
	USB	YES x 2 (Multi Media & Wireless Mouse and Keyboard)
	CI	N/A
	RCA	YES x 1
	RJ45	YES x 1
	Micro SD card	YES x 1

<b>Andriod</b>	SOC	AMLogic 962, ARM Cortex A53 quad core CPU @1.5GHz
	RAM	2GB DDR4
	GPU	5 core ARM Mali-450
	Built-in Flash	8GB
	Wi-Fi	YES x 1
	OS	Android 7

<b>Other Features</b>	APS	DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Francais, Espanol, Portugese, Italian.
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES
	Wifi on Android	YES
	Hotel Mode	N/A

<b>Power</b>	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	155W
	KWh/annum	226kWh
	Max power Consumption	220W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	A

<b>Accessories</b>	QSG	YES x 1
	Remote Control	YES x 1
	Power Cable	YES x 1
	Warranty	YES x 1
	Battery	1.5V(AAA) x2

<b>Dimension</b>	Unit Dimension With Stand (W x D x H mm)	1462 x 275 x 897
	Unit Dimension Without Stand (W x D x H mm)	1462 x 88 x 845
	Weight of unit (kg)	27.8