

Full screen 5.5" smartphone featuring fingerprint scanner, 4G support and slim body



Touch ID



IPS 2.5D Display



Full Screen



8.0MP AF with Flash



LTE-A



3000mAh battery



- Full screen experience: see more and hold less with 5.5" IPS display with 18:9 aspect ratio. Enjoy the comfort of bezel-less phone with HD-resolution
- Fingerprint scanner: protects your data in a more reliable and intelligent way
- Beautiful design: slim body together with 2.5D curved screen glass ensure gorgeous look. Smartphone is available in trendy color options: red, blue and black
- Speed in your palm: 4G LTE Internet connection gives you ability to do more: streaming without interruption, seamlessly playing multi-player games and browsing faster than ever before
- Photo and video: advanced 8.0MP AF camera with LED-flash ensures excellent clear & vivid shots
- High performance multitasking and energy saving: based on quad core processor and 1GB RAM
- Dual SIM: for optimizing budget on calls and Internet

SIM card slot	Dual SIM: LTE + WCDMA
Display	Size: 5.5" Resolution: HD-, (1280x640), 18:9 Technology: IPS, 2.5D curved glass
Processor	SC9832 1.3GHz quad core
Memory	Built-in: 1 GB RAM + 8 GB eMMC Expandable: slot for microSD™ card up to 32GB
Power	3000 mAh Li-ion battery
OS	Android 7.0 Nougat
Imaging	Front: 2.0MP with flash light Rear: 8.0MP AF with flash light

Network	4G LTE: 800/1800/2600 MHz 3G WCDMA: 900/2100MHz 2G GSM: 850/900/1800/1900MHz
Connectivity	BT 4.0+HS, Wi-Fi: 802.11b/g/n USB: microUSB 2.0
Audio	Mic, speakers, 3.5 jack
Built-in devices	Fingerprint scanner, GPS, FM
Dimensions	155 x 71 x 9.2 mm
Weight	169g (with battery)
In the box	USB cable, AC charger, screen protective film