




Suppliers of Quality Assured Cables

Audio Cable Flat Profile 4 Core Speaker Cable



Product Type:
Audio Cable

Application:

These cables are high quality, extra flexible, flat profile, OFC speaker cable for high power in-car and domestic Hi-Fi installations. They have very flexible conductors, flexible PVC insulation and individual core marking which results in a cable that is easy to route with clear core polarity marking for phasing

Standards / Conformances:

- REACH & RoHS Compliant

Construction:

Conductor:	Plain oxygen free copper; 126/0.1mm
Insulation:	PVC; flat section with separation grooves Colour : Grey Individual cores print : R - R + L - L+

Technical Information:

Cable dimensions	2.6mm x 14.0mm
Conductor resistance	≤18.8 Ω/km @ 20°C
Insulation resistance	≥200 MΩ.km @ 20°C
Operating Temperature	70°C max
Rated voltage	100V